

Hygienic, Low-Flow Cleaning that meet 3-A standards

Alfa Laval TJ SaniMagnum SB/3-A Rotary Spray Head

Application

The Alfa Laval Toftejorg SaniMagnum SB Rotary Spray Head is designed with respect to Self-Cleaning, Self-Draining and Inspectability. Its novel patented One-clip assembly offers easy installation, disassembly and inspection without compromising cleanability and drainability. The Toftejorg SaniMagnum SB is an efficient replacement for the traditional Static Spray Ball as it offers liquid impact on the entire tank wall that lies within the spray pattern – a 270°U or a 360° pattern; both at a lower flow rate at equally low pressure.

Working principle

The flow of cleaning media causes the head of the Toftejorg SaniMagnum SB to rotate on a liquid film (Slide Bearing), with fans of water laid out in a swirling pattern on the entire perimeter within the spray pattern. This generates a vibrating impact in the impact zone and a dynamic cascading flow that covers all internal surfaces of the tank, vessel or reactor. The Self-Cleaning feature is due to the unique design that includes cleaning of the down pipe.



TECHNICAL DATA

Lubricant: Lubrication by rinse/cleaning fluid
 Wetting radius: Max. 4.5 m
 Impact cleaning radius: Max. 2.4 m
 Steam or gas (air): Not supported – contact AL

Pressure

Working pressure: 1-3 bar
 Recommended pressure: 2 bar

Spray Pattern



360°



270° up

Standard Design

The Toftejorg SaniMagnum SB can be supplied with 3.1 Certificates for metallic parts and 3-A Conformity* on its plastic part.

*Implies that the material complies with FDA 21CFR.

Sizing/selection and installation drawing are available. Contact Alfa Laval for recommendations.

PHYSICAL DATA

Materials

Metalic parts: 316L
 Non-metallic parts: PEEK 450G
 Surface finish: Ra 0.8 µm

Temperature

Max. working temperature: 95°C
 Max. ambient temperature: 150°C

Weight: 0.4 kg

Connections

Clip-on: 1½" BPE US, 1½" ISO 2037
 Weld-on: 2" BPE US*

Clip

Easy-on/off clip (Ø4.0 mm)

Clip needed for both clip-on and weld-on versions to assemble the machine.

Recommended tank size: 23-68 m³

Certificates

2.2 Material Certificate and EHEDG and 3-A
 As add-on: 3.1 Material Certificate and ATEX.

