

For 1/2", 5/8" O.D. Tube  
**MODEL NO. QTM-2**  
**MAC**  
DIVERSiTECH

**MAC FEATURES**  
**UNI-PORT**  
1 Connection for  
Piercing & Servicing

B12-411

**MAC**  
**ADJUSTABLE**  
**LINE TAP VALVE**

After Servicing,  
Needle Automatically  
Back-Seats, Leaving  
Line 100% Free  
of Restrictions

DIVERSiTECH  
**DIVERSITECH**  
Duluth, GA



**RESISTS TEMPERATURE**  
**TO 300°**

**FEATURES:**

2 Socket Head Screws.  
Hex Wrench Included.

Needle Automatically  
Retracts.

Pierces Easily By Hand.

Sealed With O Rings.

Refuses To Leak.

Designed in USA  
Made in China

DIVERSiTECH  
**MAC**  
**MODEL NO. QTM-2**  
For 1/2", 5/8" O.D. Tube